


Molle carico medio
Medium load springs
Federn für mittlere belastung
Ressorts charge moyenne

Serie
Series
Serie
Série

B

ISO 10243



D _H	D _d	L ₀	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	Rigidità Rate Rigidez Raideur	25%		30%		37,5%		D	
					3.000.000	1.500.000	Max. Defl.		Approx.			
b x h				N / mm	mm	N	mm	N	mm	N	mm	N
mm	mm	mm										
10	5	25	B 10 - 025	16.0	6.3	101	7.5	120	9.4	150	10.2	163
		32	B 10 - 032	13.0	8.0	104	9.6	125	12.0	156	14.2	185
		38	B 10 - 038	11.9	9.5	113	11.4	136	14.3	170	16.8	200
		44	B 10 - 044	10.3	11.0	113	13.2	136	16.5	170	19.4	200
		51	B 10 - 051	8.9	12.8	114	15.3	136	19.1	170	23.4	208
		64	B 10 - 064	7.5	16.0	120	19.2	144	24.0	180	28.2	212
		76	B 10 - 076	5.3	19.0	101	22.8	121	28.5	151	34.2	181
		305	B 10 - 305	1.6	76.3	122	91.5	146	114.4	183	133.8	214
12.5	6.3	25	B 13 - 025	30.0	6.3	189	7.5	225	9.4	282	11.9	357
		32	B 13 - 032	24.8	8.0	198	9.6	238	12.0	298	16.2	402
		38	B 13 - 038	21.4	9.5	203	11.4	244	14.3	306	18.7	400
		44	B 13 - 044	18.5	11.0	204	13.2	244	16.5	305	21.3	394
		51	B 13 - 051	15.5	12.8	198	15.3	237	19.1	296	25.6	397
		64	B 13 - 064	12.1	16.0	194	19.2	232	24.0	290	32.4	392
		76	B 13 - 076	10.2	19.0	194	22.8	233	28.5	291	39.0	398
		305	B 13 - 305	2.1	76.3	160	91.5	192	114.4	240	152.5	320
16	8	25	B 16 - 025	49.4	6.3	311	7.5	371	9.4	464	10.5	519
		32	B 16 - 032	37.1	8.0	297	9.6	356	12.0	445	13.2	490
		38	B 16 - 038	33.9	9.5	322	11.4	386	14.3	485	17.2	583
		44	B 16 - 044	30.0	11.0	330	13.2	396	16.5	495	19.4	582
		51	B 16 - 051	26.4	12.8	338	15.3	404	19.1	504	24.2	639
		64	B 16 - 064	20.5	16.0	328	19.2	394	24.0	492	29.2	599
		76	B 16 - 076	17.8	19.0	338	22.8	406	28.5	507	36.3	646
		305	B 16 - 305	4.8	76.3	366	91.5	439	114.4	549	141.6	680
20	10	25	B 20 - 025	98.0	6.3	617	7.5	735	9.4	921	10.5	1029
		32	B 20 - 032	72.6	8.0	581	9.6	697	12.0	871	13.9	1009
		38	B 20 - 038	56.0	9.5	532	11.4	638	14.3	801	16.6	930
		44	B 20 - 044	47.5	11.0	523	13.2	627	16.5	784	18.8	893
		51	B 20 - 051	41.7	12.8	534	15.3	638	19.1	796	23.1	963
		64	B 20 - 064	32.3	16.0	517	19.2	620	24.0	775	27.5	888
		76	B 20 - 076	25.1	19.0	477	22.8	572	28.5	715	33.8	848
		89	B 20 - 089	22.0	22.3	491	26.7	587	33.4	735	39.7	873
		102	B 20 - 102	19.8	25.5	505	30.6	606	38.3	758	47.3	937
		115	B 20 - 115	18.1	28.8	521	34.5	624	43.1	780	52.5	950
		127	B 20 - 127	16.6	31.8	528	38.1	632	47.6	790	56.9	945
		139	B 20 - 139	15.1	35.0	529	42.0	634	52.5	793	62.1	938
		152	B 20 - 152	13.2	38.0	500	45.6	600	57.0	750	67.6	889
		305	B 20 - 305	6.1	76.3	465	91.5	558	114.4	698	143.4	875

Note: 1 N = 0,102 Kg (force)

Colore blu
Blue color
Kennfarbe blau
Couleur bleu



D _H	D _d	L ₀	N. di catalogo Catalogue No. Bestellnummer N° de catalogue	Rigidità Rate Rigidez Raideur	25%		30%		37,5%		D	
					3.000.000		1.500.000		Max. Defl.		Approx.	
b x h				N / mm	mm	N	mm	N	mm	N	mm	N
mm	mm	mm										
25	12.5	25	B 25 - 025	147	6.3	926	7.5	1103	9.4	1382	10.2	1499
		32	B 25 - 032	118	8.0	944	9.6	1133	12.0	1416	13.7	1617
		38	B 25 - 038	93.0	9.5	884	11.4	1060	14.3	1330	15.7	1460
		44	B 25 - 044	80.8	11.0	889	13.2	1067	16.5	1333	18.2	1471
		51	B 25 - 051	68.6	12.8	878	15.3	1050	19.1	1310	21.7	1489
		64	B 25 - 064	53.0	16.0	848	19.2	1018	24.0	1272	26.0	1378
		76	B 25 - 076	43.2	19.0	821	22.8	985	28.5	1231	32.3	1395
		89	B 25 - 089	38.2	22.3	852	26.7	1020	33.4	1276	38.0	1452
		102	B 25 - 102	33.0	25.5	842	30.6	1010	38.3	1264	43.0	1419
		115	B 25 - 115	28.0	28.8	806	34.5	966	43.1	1207	48.6	1361
		127	B 25 - 127	25.9	31.8	824	38.1	987	47.6	1233	53.7	1391
		139	B 25 - 139	23.2	35.0	812	42.0	974	52.5	1218	59.4	1378
		152	B 25 - 152	20.8	38.0	790	45.6	948	57.0	1186	63.8	1327
178	B 25 - 178	17.8	44.5	792	53.4	951	66.8	1189	76.6	1363		
203	B 25 - 203	15.8	50.8	803	60.9	962	76.1	1202	88.4	1397		
305	B 25 - 305	10.2	76.3	778	91.5	933	114.4	1167	135.1	1378		
5.4 x 3.3												
32	16	38	B 32 - 038	185	9.5	1758	11.4	2109	14.3	2646	16.3	3016
		44	B 32 - 044	158	11.0	1738	13.2	2086	16.5	2607	18.9	2986
		51	B 32 - 051	134	12.8	1715	15.3	2050	19.1	2559	23.1	3095
		64	B 32 - 064	99.0	16.0	1584	19.2	1901	24.0	2376	28.5	2822
		76	B 32 - 076	80.5	19.0	1530	22.8	1835	28.5	2294	34.2	2753
		89	B 32 - 089	69.1	22.3	1541	26.7	1845	33.4	2308	40.4	2792
		102	B 32 - 102	58.8	25.5	1499	30.6	1799	38.3	2252	48.0	2822
		115	B 32 - 115	51.5	28.8	1483	34.5	1777	43.1	2220	54.3	2796
		127	B 32 - 127	44.8	31.8	1425	38.1	1707	47.6	2132	59.2	2652
		139	B 32 - 139	42.3	35.0	1481	42.0	1777	52.5	2221	65.3	2762
		152	B 32 - 152	37.8	38.0	1436	45.6	1724	57.0	2155	73.0	2759
		178	B 32 - 178	32.5	44.5	1446	53.4	1736	66.8	2171	84.5	2746
		203	B 32 - 203	28.9	50.8	1468	60.9	1760	76.1	2199	96.9	2800
254	B 32 - 254	21.4	63.5	1359	76.2	1631	95.3	2039	120.9	2587		
305	B 32 - 305	18.3	76.3	1396	91.5	1674	114.4	2094	146.9	2688		
6.8 x 4.0												
40	20	51	B 40 - 051	181.6	12.8	2324	15.3	2778	19.1	3469	21.4	3886
		64	B 40 - 064	140.0	16.0	2240	19.2	2688	24.0	3360	26.8	3752
		76	B 40 - 076	108.0	19.0	2052	22.8	2462	28.5	3078	32.7	3532
		89	B 40 - 089	90.7	22.3	2023	26.7	2422	33.4	3029	39.0	3537
		102	B 40 - 102	81.0	25.5	2066	30.6	2479	38.3	3102	44.1	3572
		115	B 40 - 115	71.8	28.8	2068	34.5	2477	43.1	3095	50.6	3633
		127	B 40 - 127	62.7	31.8	1994	38.1	2389	47.6	2985	55.9	3505
		139	B 40 - 139	57.5	35.0	2013	42.0	2415	52.5	3019	61.8	3554
		152	B 40 - 152	51.6	38.0	1961	45.6	2353	57.0	2941	67.5	3483
		178	B 40 - 178	44.1	44.5	1962	53.4	2355	66.8	2946	77.2	3405
		203	B 40 - 203	36.7	50.8	1864	60.9	2235	76.1	2793	91.8	3369
		254	B 40 - 254	30.1	63.5	1911	76.2	2294	95.3	2869	112.7	3392
		305	B 40 - 305	24.6	76.3	1877	91.5	2251	114.4	2814	138.1	3397
8.2 x 4.7												
50	25	64	B 50 - 064	209	16.0	3344	19.2	4013	24.0	5016	28.2	5894
		76	B 50 - 076	168	19.0	3192	22.8	3830	28.5	4788	34.9	5863
		89	B 50 - 089	140	22.3	3122	26.7	3738	33.4	4676	39.2	5488
		102	B 50 - 102	119	25.5	3035	30.6	3641	38.3	4558	47.3	5629
		115	B 50 - 115	106	28.8	3053	34.5	3657	43.1	4569	52.6	5576
		127	B 50 - 127	97.0	31.8	3085	38.1	3696	47.6	4617	59.8	5801
		139	B 50 - 139	87.0	35.0	3045	42.0	3654	52.5	4568	65.1	5664
		152	B 50 - 152	80.0	38.0	3040	45.6	3648	57.0	4560	70.8	5664
		178	B 50 - 178	69.5	44.5	3093	53.4	3711	66.8	4643	84.2	5852
		203	B 50 - 203	59.8	50.8	3038	60.9	3642	76.1	4551	96.5	5771
		229	B 50 - 229	50.9	57.3	2917	68.7	3497	85.9	4372	108.5	5523
		254	B 50 - 254	43.9	63.5	2788	76.2	3345	95.3	4184	121.8	5347
		305	B 50 - 305	38.6	76.3	2945	91.5	3532	114.4	4416	146.8	5666
11.1 x 5.8												
63	38	76	B 63 - 076	312	19.0	5928	22.8	7114	28.5	8892	30.7	9578
		89	B 63 - 089	260	22.3	5798	26.7	6942	33.4	8684	36.5	9490
		102	B 63 - 102	221	25.5	5636	30.6	6763	38.3	8464	43.6	9636
		115	B 63 - 115	187	28.8	5386	34.5	6452	43.1	8060	48.9	9144
		127	B 63 - 127	168	31.8	5342	38.1	6401	47.6	7997	54.2	9106
		152	B 63 - 152	136	38.0	5168	45.6	6202	57.0	7752	65.7	8935
		178	B 63 - 178	114	44.5	5073	53.4	6088	66.8	7615	76.5	8721
		203	B 63 - 203	100	50.8	5080	60.9	6090	76.1	7610	88.0	8800
		229	B 63 - 229	89.2	57.3	5111	68.7	6128	85.9	7662	103.9	9268
		254	B 63 - 254	78.4	63.5	4978	76.2	5974	95.3	7472	112.4	8812
305	B 63 - 305	64.7	76.3	4937	91.5	5920	114.4	7402	133.8	8657		
11.5 x 9.1												

